



What is LIPOSLIM™?

Easy to use

Minimal noise and heat

Safe and compact design



LIPOSLIM™

Strong power of 5,000rpm but low noise and low vibration system offers familiar operation environment

Advantages

- Strong power : 5,000rpm
- High technology motor and controller improve its durability and decrease heat innovatively
- High durability by journal bearing system.
- A handpiece with a built-in fat outlet improves operation management.
- Fat outlet is separated for easy sterilization and reuse.
This can be visually confirmed through silicone outlet
- Strong and solid duralumin based consol and handpiece case
- Internally equipped triple soundproof design performs ultra low noise system
- Self locking system prevents cable disconnection while using
- Triple safety system with POWER SUPPLY, AMP CONTROL, and 2nd fuse
- Specially plated exterior color of consol and handpiece maintains its original color despite of long time use.
- One-touch button makes easy change of CONTINUE / FOOT SWITCH
- Easy control of strength with Jog-dial.
- Easy to confirm presently using power on LED display window.

Specification

- Reciprocation : Max 5,000rpm
- Stroke : 2.5mm

▼ PRODUCT SET



Handpiece



Cannula



Lipo-Cable



Foot Switch



Power Cord